

Mineral white lens 1.523

Progressive INSIGHT


Index of refraction	1.523	Treatments:	MC
Abbe value	59		
Density (g/cm ³)	2.55		
UVB protection	100%		
UVA protection	50%		
Filter category	0		
Use on the road during the day	Yes		
Use on the road during the night	Yes		

Fitting high 22mm

Rx Lab Mineral white 1.523 Progressive INSIGHT	Power range (sph. + cyl. added)			Add		Diameter (mm)
	Min	Max	Max. Cyl	Min	Max	
	-6.00	+7.00	4.00	0.75	3.50	60-70 (max. 70/75)

- Progressives intended for presbyopic correction with typical configuration:
 1. Distance zone
 2. Near zone
 3. Intermediate corridor
- With respect to its fitting, it is necessary that a vertical distance from the center of pupil to the lower edge of frame is longer than stated fitting high, in order to enable the user with appropriate correction and satisfactory width of visual field.

PROGRESSIVE INSIGHT



Lenses meet the requirements of standards ISO 14889:2003; ISO 8980-1:2004; ISO 8980-2:2004; ISO 8980-3:2003; ISO 8980-4:2000. The production is in compliance with the requirements of the production of medical I class device pursuant to Directive of European Union 93/42 CEE.

OPHTHALMIC LENSES CATALOG 2010/2011

www.grossoptic.com

065