

Transitions VI 1.60 Gray & Brown

Index of refraction	1.60	Treatments:	HC (included in the price)
Abbe value	42		MC
Density (g/cm ³)	1.29		Satin Coat Plus
UVB protection	100%		
UVA protection	100%		
Filter category	0 faded 3 darkened		

Use on the road during the day Yes

Use on the road during the night Yes

- Light photosensitive lenses comfortable for wearing regardless of the frame type or lighting conditions.
- They react quickly to changes in lighting conditions and give 100% eye protection in indoor (office) and outdoor surroundings.
- Protection layer against scratching (HC) is necessary and it is included in the price. Also it is recommended to apply antirreflection multicoating or satin coat plus (MC/SCP) for enhancement of picture quality.
- In an inactive condition, with HMC layer, they are more transparent than organic lens 1.50 without HMC.
- Tinting and ERP layer applying are not recommended.

Rx Lab Transitions VI 1.60 Gray & Brown HC Spheric	Power range (sph. + cyl. added)			Diameter (mm)
	Min	Max	Max. Cyl.	50-72
	-14.00	+8.00	5.25	45.00

Rx Lab Transitions VI 1.60 Gray & Brown HC Aspheric	Power range (sph. + cyl. added)			Diameter (mm)
	Min	Max	Max. Cyl.	50-72
	-8.00	+5.00	4.00	47.00



RECOMMENDATION:

Follow the instructions for fitting of high index organic lenses, page no.87